



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Signal insert D-Sub, 25-pole, Socket / solder connection
Order No.	1450900000
Type	IE-FCI-D25-FS
GTIN (EAN)	4050118255560
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	15.3 mm	Height (inches)	0.6024 inch
Width	12.5 mm	Width (inches)	0.4921 inch
Length	53.1 mm	Length (inches)	2.0905 inch
Net weight	13.05 g		

Temperatures

Storage temperature	Operating temperature	-55 °C...105 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a1
REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

Technical data

Number of poles	25	Contact surface	Gold-plated
Contact resistance	≤ 20 mΩ	Dielectric strength, contact / contact	1 kV eff /1 min.
Housing main material	SPCC	Insulation resistance	1000 MΩ at 500 V DC
Material insulator	PBT glass fibre reinforced UL 94 V-0	Housing surface	tin-plated
Current-carrying capacity	1 A		

General data

Protection degree	IP20	Insert type	Signal insert D-Sub, 25-pole
-------------------	------	-------------	------------------------------

Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / contact	1 kV eff /1 min.
Insulation resistance	1000 MΩ at 500 V DC		

General standards


Certificate No. (DNV)	TAA000022B
-----------------------	------------

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

Drawings

Dimensioned drawing



Dimensioned drawing

