

**VG M25 EXE MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Brass cable glands which are suitable for usage in explosion risk zone Ex e (Increased safety). They have been tested to the latest norms and standards IEC/EN 60079-0, and also achieved the necessary ATEX certificate.

**General ordering data**

Version	VG Ex MS (Ex brass cable gland), Cable glands, straight, M 25, 16 mm, OD min. 10 - OD max. 18 mm, IP66, IP68, Brass, nickel-plated
Order No.	<a href="#">1460070000</a>
Type	VG M25 EXE MS
GTIN (EAN)	4050118266214
Qty.	20 items

## VG M25 EXE MS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals	CE
Approvals	EAC; ATEX
Approvals	
ROHS	Conform

## Dimensions and weights

Height	45.5 mm	Height (inches)	1.7913 inch
Length	45.5 mm	Length (inches)	1.7913 inch
Net weight	64.4 g		

## Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

## Certificate numbers cable gland

Identification	Ex d IIC Gb, Ex e IIC Gb, Ex tb IIC Db IP66/68	Certificate no. cable gland (ATEX)	IMQ 11 ATEX 038 X
Certificate no. cable gland (GOST)	POCC TR.05.B04161		

## General information

Outer cable diameter, max.	18 mm	Outer cable diameter, min.	10 mm
O-Ring	NBR	Protection degree with GWDR	IP66, IP68
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-7, EN 60079-11, EN 60079-31	AF size 1	28 mm
AF size 2	28 mm	Protection degree	IP66, IP68 - 6 bar (30 min.)
Cable gland	metric	Basic material	Brass, nickel-plated
Seal insert	CR	External thread	M 25
Length of thread	16 mm	Note: protection class	Please observe the information in the installation instructions.
Installation guidelines	See assembly instructions	Clamp insert	Neoprene

## Important note

Product information	For enclosure wall thicknesses less than or equal to 3 mm (e.g. Klippon STB enclosures), an additional flat gasket must be used - GWDR NP. Additional flat gaskets are included in the packaging unit.
---------------------	--

**Technical data**

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

## VG M25 EXE MS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

Type	SKMU M25 MS	Version	
Order No.	<a href="#">1737010000</a>	SKMU MS (brass locknut), Locknut, M 25, 3.5 mm, Brass, nickel-	
GTIN (EAN)	4008190956486	plated	
Qty.	100 ST		