


## RS F20 X3 OUT



The interfaces for redundancy are supplied with various IEC 60603-13 connectors. This enables various controllers to work in parallel, although not simultaneously, with the new system being tested.

### General ordering data

Order No.	1461220000
Type	<a href="#">RS F20 X3 OUT</a>
GTIN (EAN)	4050118266955
Qty.	1 items

## RS F20 X3 OUT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	70 mm	Height (inches)	2.7559 inch
Width	40 mm	Width (inches)	1.5748 inch
Net weight	75 g		

## Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a
REACH SVHC	Lead 7439-92-1
SCIP	7b5ffb72-271d-4c73-8b09-bd0aeee3697a

## Connection Data

Number of poles (control side)	20-pole	Earthing	No
Connection on control side	3 x plug-in connectors in acc. with IEC60603-13 / DIN41651		

## Rating data

Rated voltage	50 V AC / 70 V DC	Rated current per connection	0.5 A
Total operating current	3 A		

## Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	50 V AC / 70 V DC
Surge voltage category	II	Pollution severity level	2
Insulation test voltage AC	0.35 kV		

## Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		