

**VGM25-MS68 EMC 11-20SET****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

**General ordering data**

Version	Accessories
Order No.	<a href="#">1463720000</a>
Type	VGM25-MS68 EMC 11-20SET
GTIN (EAN)	4050118269871
Qty.	1 items

**VGM25-MS68 EMC 11-20SET**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

RoHS	Conform
------	---------

**Dimensions and weights**

Length	63.5 mm	Length (inches)	2.5 inch
Net weight	94.44 g		

**Temperatures**

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

**General information**

Outer cable diameter, max.	20 mm	Outer cable diameter, min.	11 mm
O-Ring	NBR	Protection degree with GWDR	IP68
Operating temperature range, max.	130 °C	Operating temperature range, min.	-40 °C
Halogen	halogen-free	Standards	EN 45545-2:2013
AF size	30 mm	Protection degree	IP68 - 15 bar
Cable gland	M 25, EMV	Basic material	Brass, nickel-plated
External thread	M 25	Length of thread	7.5 mm

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

**VGM25-MS68 EMC 11-20SET**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****HDC mounting tool**

Weidmüller's professional tools are the result of an intensive development process that has been specifically focussed on the requirements of their use in practice. We offer many useful tools, e.g. no-contact tools, crimping pliers and fibre optic tools, that help you work safely and precisely for an optimised installation of heavy-duty connectors.

**General ordering data**

Type      **HDC FBS TOOL 13-50**

Order No.      [8000015137](http://www.weidmueller.com/8000015137)

GTIN (EAN)      4050118292947

Qty.      1 ST

Version

Mounting tool