

STRIPAX ULTIMATE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	1468880000
Type	STRIPAX ULTIMATE
GTIN (EAN)	4050118274158
Qty.	1 items

STRIPAX ULTIMATE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	174.63 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Wire stripper unit
------------------------	--------------------

Stripping tools

Cable type	Flexible and solid conductors with halogen-free insulation	Conductor cross-section (cutting capacity)	6 mm ²
Stripping range AWG, max.	10 AWG	Stripping range AWG, min.	24 AWG
Stripping length, max.	25 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.25 mm ²		

Classifications


ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06
ECLASS 13.0	21-04-37-06	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

STRIPAX ULTIMATE


Drawings



Example of use




Example of use



TYPE THHN 6

ALOGEN FREE 2,5MM² H07Z-K

STRIPAX ULTIMATE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Accessories****Accessories / replacement parts**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	ERME SPX UL	Version
Order No.	1471390000	Accessories, Cutter holder
GTIN (EAN)	4050118278248	
Qty.	1 ST	
Type	ERTE KLBC SPX UL	Version
Order No.	2571500000	Accessories, Replacement clamping jaw
GTIN (EAN)	4050118582123	
Qty.	1 ST	