

**STRIPAX ULTIMATE****Weidmüller Interface GmbH & Co. KG**

Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">1468880000</a>
Type	STRIPAX ULTIMATE
GTIN (EAN)	4050118274158
Qty.	1 items

## STRIPAX ULTIMATE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	174.63 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Technical data

Description of article	Wire stripper unit
------------------------	--------------------

## Stripping tools

Cable type	Flexible and solid conductors with halogen-free insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
Stripping range AWG, max.	10 AWG	Stripping range AWG, min.	24 AWG
Stripping length, max.	25 mm	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

## STRIPAX ULTIMATE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Drawings



#### Example of use



#### Example of use



TYPE THHN

ALOPEN FREE 2.5MM<sup>2</sup> H07Z-K

## STRIPAX ULTIMATE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Accessories / replacement parts



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

## General ordering data

Type	ERME SPX UL	Version
Order No.	<a href="#">1471390000</a>	Accessories, Cutter holder
GTIN (EAN)	4050118278248	
Qty.	1 ST	
Type	ERTE KLBC SPX UL	Version
Order No.	<a href="#">2571500000</a>	Accessories, Replacement clamping jaw
GTIN (EAN)	4050118582123	
Qty.	1 ST	