

CC-M 70/48 ST SDR


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | MetalliCard, Device markers, 70 x 48 mm, silver |
| Order No. | 1474380000 |
| Type | CC-M 70/48 ST SDR |
| GTIN (EAN) | 4050118290394 |
| Qty. | 1 items |

CC-M 70/48 ST SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.5 mm | Depth (inches) | 0.0197 inch |
| Height | 70 mm | Height (inches) | 2.7559 inch |
| Width | 48 mm | Width (inches) | 1.8898 inch |
| Net weight | 17.4 g | | |

Temperatures

Operating temperature range -55...130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--------------------------------------|--|-------------|--|
| Version | pluggable | | |
| Width | 48 mm | | |
| Operating temperature range, max. | 130 °C | | |
| Operating temperature range, min. | -55 °C | | |
| Colour | silver | | |
| Basic material | Micro-etched stainless steel 1.4301 (ST), Stainless steel 1.4301 | | |
| Printed characters | Requires M-Print PRO File | | |
| Number of markers per packaging unit | Form of supply | MetalliCard | |
| Size of labelling field | 68 x 46 mm | | |
| compatible printer | | | |
| Number of markers per combination | 1 MetalliCard = Device markers | | |
| Operating temperature range | -55...130 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

CC-M 70/48 ST SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

