


H4,0/18D GR SP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



- supplied loose in poly-bag
- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
Order No.	1476290000
Type	H4,0/18D GR SP
GTIN (EAN)	4050118283204
Qty.	100 items
Packaging	Multipack bag

H4,0/18D GR SP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

Dimensions and weights

Net weight	0.22 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, grey	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	10 mm
Collar diameter (D2)	4.8 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	18.00 mm	Wire connection cross section AWG, max.	AWG 12
Metal sleeve thickness (S1)	0.2 mm	Stripping length	12 mm
Conductor cross-section	4 mm ²	Colour code	DIN

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawings

Drawing

