

**HSS 3.2-9.5 EL Y13M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|            |   |
|------------|---|
| Version    | Conductor and cable markers, 3.2 - 9.5 mm, yellow |
| Order No.  | <a href="#">1489570000</a>                        |
| Type       | HSS 3.2-9.5 EL Y13M                               |
| GTIN (EAN) | 4050118299199                                     |
| Qty.       | 1 items   |

## HSS 3.2-9.5 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E366310                    |

### Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 0.77 mm  | Depth (inches)  | 0.0303 inch |
| Width      | 15.1 mm  | Width (inches)  | 0.5945 inch |
| Length     | 13000 mm | Length (inches) | 511.81 inch |
| Net weight | 182 g    |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |  |                                   |   |
|-----------------------------------|--|-----------------------------------|---|
| Type of printing                  | neutral  | Width                             | 15.1 mm   |
| Operating temperature range, max. | 135 °C   | Operating temperature range, min. | -55 °C  |
| Colour                            | yellow   | Halogen                           | Yes   |
| Length                            | 13000 mm   | Basic material                    | Polyolefine   |
| Printed characters                | without  | Recommended industries            | Plant manufacture, Energy, Device manufacturer, Machinery |
| compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> | Operating temperature range       | -55...135 °C  |

### Conductor and cable markers

|                                   |                        |                               |                    |
|-----------------------------------|------------------------|-------------------------------|--------------------|
| Halogen                           | Yes                    | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min.     | 4 mm <sup>2</sup>      | Conductor O.D., max.          | 9.5 mm             |
| Conductor O.D., min.              | 3.2 mm                 | Rate of shrinkage             | 3:1                |
| Recommended shrinking temperature | 90 °C                  | Text field width              | 0 mm               |
| Text field height                 | 14.9 mm                | Conductor O.D.                | 3.2 - 9.5 mm       |
| Cross-section for connected wire  | 4 - 16 mm <sup>2</sup> |                               |                    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



## HSS 3.2-9.5 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |            |  |
|------------|----------------------------|------------|--|
| Type       | RIBBON HSS HF EL 40/300... | Version    |  |
| Order No.  | <a href="#">1426210000</a> | Ink ribbon |  |
| GTIN (EAN) | 4050118228823              |            |  |
| Qty.       | 1 ST                       |            |  |

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | MULTIMARK ROLLER 115       | Version |  |
| Order No.  | <a href="#">1357420000</a> |         |  |
| GTIN (EAN) | 4050118160314              |         |  |
| Qty.       | 1 ST                       |         |  |
| Type       | MULTIMARK ROLLER 30        | Version |  |
| Order No.  | <a href="#">1357430000</a> |         |  |
| GTIN (EAN) | 4050118160253              |         |  |
| Qty.       | 1 ST                       |         |  |