



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 16 mm <sup>2</sup> , 16 mm <sup>2</sup> - 16 mm <sup>2</sup>
Order No.	<a href="#">1491350000</a>
Type	KQIG-M6/-16
GTIN (EAN)	4050118300987
Qty.	50 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Net weight	5.84 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor cross-section	16 mm <sup>2</sup>	Insulation	Available
Material/plastic	PA	Hole	C 6
Identification colour	blue	Inside diameter of shaft (d1)	5.8 mm
Outside diameter of shaft (d3)	11 mm	Connection length (l)	32.2 mm
Inside diameter of flange (d2)	6.5 mm	Inside diameter of collar (d4)	11 mm

**Classifications**

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

