

KSI/-10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ²
Order No.	1491430000
Type	KSI/-10
GTIN (EAN)	4050118301403
Qty.	50 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	3 g
------------	-----

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connectors

Conductor cross-section, max.	10 mm ²	Conductor cross-section	10 mm ²
Insulation	Available, PA	Material/plastic	PA
Length 1 (l1)	34 mm	Identification colour	red
Inside diameter of shaft (d1)	4.5 mm	Length 2 (l2)	12 mm
Outside diameter of shaft (d3)	2.4 mm	Inside diameter of collar (d4)	7.8 mm

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

