



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.14 mm ² - 0.5 mm ² , yellow
Order No.	1491490000
Type	VSRI/0,1-0,5
GTIN (EAN)	4050118301533
Qty.	50 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.52 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connectors

Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.14 mm ²
Insulation	Fully insulated	Material/plastic	Polyolefine
Length 1 (I1)	24.5 mm	Identification colour	yellow
Inside diameter of shaft (d1)	1.4 mm	Length 2 (I2)	11.5 mm
Inside diameter of collar (d4)	3.1 mm		

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

