



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup> , red
Order No.	<a href="#">1491510000</a>
Type	VSRI/0,5-1,0
GTIN (EAN)	4050118300963
Qty.	50 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Net weight	1.1 g
------------	-------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section, max.	1 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Insulation	Fully insulated	Material/plastic	Polyethylene
Length 1 (I1)	36 mm	Identification colour	red
Inside diameter of shaft (d1)	1.7 mm	Length 2 (I2)	15 mm
Inside diameter of collar (d4)	4.4 mm		

**Classifications**

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

