



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1 mm ² , red
Order No.	1491770000
Type	VSTVI/0,5-1,0
GTIN (EAN)	4050118301465
Qty.	100 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 1.25 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 7b42d2b9-0a0f-4f66-a989-e9bfbbfeb1b3

Connectors

Conductor cross-section, max.	1 mm ²	Conductor cross-section, min.	0.5 mm ²
Conductor cross-section	1 mm ²	Insulation	Available, Partially insulated
Material/plastic	PVC	Length 1 (l1)	23.9 mm
Identification colour	red	Plug-in width (d2)	6.3 mm
Plug-in density (d3)	0.8 mm	Length 3 (l3)	8.2 mm

Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

Drawings

