

FSKI/4,0-6,0/638

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Insulated tab connector made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6 mm ² , yellow
Order No.	1491840000
Type	FSKI/4,0-6,0/638
GTIN (EAN)	4050118301823
Qty.	100 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 1.71 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 7b42d2b9-0a0f-4f66-a989-e9bfbfbef1b3

Connectors

Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Conductor cross-section	6 mm ²	Insulation	Available, Partially insulated
Dimension	6.3 x 0.8 mm	Material/plastic	PVC
Length 1 (l1)	24 mm	Identification colour	yellow
Plug-in width (d2)	6.3 mm	Plug-in density (d3)	0.8 mm

Classifications

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

Drawings

