

VFSKHV/1,5-2,5/638

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Fully-insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² - 2.5 mm ² , blue
Order No.	1491940000
Type	VFSKHV/1,5-2,5/638
GTIN (EAN)	4050118301922
Qty.	100 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 1.19 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 7b42d2b9-0a0f-4f66-a989-e9bfbbfeb1b3

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Conductor cross-section	2.5 mm ²	Insulation	Fully insulated
Dimension	6.3 x 0.8 mm	Material/plastic	PVC
Length 1 (l1)	21.5 mm	Identification colour	blue
Plug-in width (d2)	6.3 mm	Plug-in density (d3)	0.8 mm

Classifications

ETIM 6.0	EC000516	ETIM 7.0	EC000516
ETIM 8.0	EC000516	ETIM 9.0	EC000516
ETIM 10.0	EC000516	ECLASS 9.0	27-44-03-92
ECLASS 9.1	27-40-02-90	ECLASS 10.0	27-44-03-92
ECLASS 11.0	27-44-03-92	ECLASS 12.0	27-44-03-92
ECLASS 13.0	27-44-03-92	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		

Drawings

