

## KQI-M4/-0,5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

### General ordering data

|                 |                                                                                                                     |
|-----------------|---------------------------------------------------------------------------------------------------------------------|
| Version         | cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> , 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup> |
| Order No.       | <a href="#">1492110000</a>                                                                                          |
| Type            | KQI-M4/-0,5                                                                                                         |
| GTIN (EAN)      | 4050118302103                                                                                                       |
| Qty.            | 100 items                                                                                                           |
| Delivery status | This article will no longer be available in the future.                                                             |
| Last order date | 2026-03-31T00:00:00+02:00                                                                                           |

## KQI-M4/-0,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 0.3 g |
|------------|-------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Connectors

|                                |                     |                                |                     |
|--------------------------------|---------------------|--------------------------------|---------------------|
| Conductor cross-section, max.  | 0.5 mm <sup>2</sup> | Conductor cross-section, min.  | 0.1 mm <sup>2</sup> |
| Conductor cross-section        | 0.5 mm <sup>2</sup> | Insulation                     | Available           |
| Material/plastic               | PA                  | Hole                           | M 4                 |
| Identification colour          | yellow              | Inside diameter of shaft (d1)  | 1 mm                |
| Outside diameter of shaft (d3) | 6.5 mm              | Connection length (l)          | 16 mm               |
| Inside diameter of flange (d2) | 4.3 mm              | Inside diameter of collar (d4) | 2.3 mm              |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001059    | ETIM 9.0    | EC001059    |
| ETIM 10.0   | EC001059    | ECLASS 14.0 | 27-40-02-12 |
| ECLASS 15.0 | 27-40-02-12 |             |             |

## Drawings

