

## KQI-M4/-6

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
Order No.	<a href="#">1492370000</a>
Type	KQI-M4/-6
GTIN (EAN)	4050118302264
Qty.	100 items

**KQI-M4/-6**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 1.6 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
Conductor cross-section	6 mm <sup>2</sup>	Insulation	Available
Material/plastic	PC	Hole	M 4
Identification colour	yellow	Inside diameter of shaft (d1)	3.6 mm
Outside diameter of shaft (d3)	8 mm	Connection length (l)	21 mm
Inside diameter of flange (d2)	4.3 mm	Inside diameter of collar (d4)	6.4 mm

**Classifications**

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

