

KQI-M5/-16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 16 mm ² , 16 mm ² - 16 mm ²
Order No.	1492480000
Type	KQI-M5/-16
GTIN (EAN)	4050118302196
Qty.	50 items

KQI-M5/-16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	4.84 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connectors

Conductor cross-section, max.	16 mm ²	Conductor cross-section, min.	16 mm ²
Conductor cross-section	16 mm ²	Insulation	Available
Material/plastic	PA	Hole	M 5
Identification colour	blue	Inside diameter of shaft (d1)	5.8 mm
Outside diameter of shaft (d3)	11 mm	Connection length (l)	31.5 mm
Inside diameter of flange (d2)	5.3 mm	Inside diameter of collar (d4)	10.5 mm

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

