

## KQI-M6/-16

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 16 mm <sup>2</sup> , 16 mm <sup>2</sup> - 16 mm <sup>2</sup>
Order No.	<a href="#">1492490000</a>
Type	KQI-M6/-16
GTIN (EAN)	4050118302455
Qty.	50 items

**KQI-M6/-16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 4.7 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor cross-section	16 mm <sup>2</sup>	Insulation	Available
Material/plastic	PA	Hole	M 6
Identification colour	blue	Inside diameter of shaft (d1)	5.8 mm
Outside diameter of shaft (d3)	11 mm	Connection length (l)	31.5 mm
Inside diameter of flange (d2)	6.5 mm	Inside diameter of collar (d4)	10.5 mm

**Classifications**

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

