



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1 mm ²
Order No.	1492530000
Type	KQIG-M3,5/-1
GTIN (EAN)	4050118302370
Qty.	100 items

KQIG-M3,5/-1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.57 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connectors

Conductor cross-section, max.	1 mm ²	Conductor cross-section, min.	0.5 mm ²
Conductor cross-section	1 mm ²	Insulation	Available
Material/plastic	PC	Hole	C 3,5
Identification colour	red	Inside diameter of shaft (d1)	1.6 mm
Outside diameter of shaft (d3)	6 mm	Connection length (l)	17 mm
Inside diameter of flange (d2)	3.7 mm	Inside diameter of collar (d4)	4 mm

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Drawings

