

**KQN-M20/-35****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end,35 mm <sup>2</sup>
Order No.	<a href="#">1493520000</a>
Type	KQN-M20/-35
GTIN (EAN)	4050118303124
Qty.	50 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Net weight	16.66 g
------------	---------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Connectors**

Conductor cross-section	35 mm <sup>2</sup>	Insulation	not available
Hole	M 20	Inside diameter of shaft (d1)	9 mm
Outside diameter of shaft (d3)	30 mm	Shaft length (a)	14 mm
Connection length (l)	37.5 mm	Inside diameter of flange (d2)	21 mm

**Classifications**

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

