

KWN-M12/-185 90**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end, 185 mm ² , 185 mm ² - 185 mm ²
Order No.	1494550000
Type	KWN-M12/-185 90
GTIN (EAN)	4050118304213
Qty.	25 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-03-31T00:00:00+02:00

KWN-M12/-185 90

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	119.32 g
------------	----------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	Euro series 90°
---------	-----------------

Connectors

Conductor cross-section, max.	185 mm ²	Conductor cross-section, min.	185 mm ²
Conductor cross-section	185 mm ²	Insulation	not available
Hole	M 12	Identification colour	None
Inside diameter of shaft (d1)	19 mm	Outside diameter of shaft (d3)	24 mm
Shaft length (a)	29 mm	Connection length (l)	28 mm
Inside diameter of flange (d2)	13 mm	Flange width (b)	35 mm

Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

KWN-M12/-185 90

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

