

KRN-M12/-185 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end, 185 mm ² , 185 mm ² - 185 mm ² |
| Order No. | 1494990000 |
| Type | KRN-M12/-185 S |
| GTIN (EAN) | 4050118304169 |
| Qty. | 10 items |

KRN-M12/-185 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 88.53 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical data

Version Euro series, narrow flange

Connectors

| | | | |
|--------------------------------|---------------------|--------------------------------|---------------------|
| Conductor cross-section, max. | 185 mm ² | Conductor cross-section, min. | 185 mm ² |
| Conductor cross-section | 185 mm ² | Insulation | not available |
| Hole | M 12 | Identification colour | None |
| Inside diameter of shaft (d1) | 18.7 mm | Outside diameter of shaft (d3) | 24 mm |
| Shaft length (a) | 30 mm | Connection length (l) | 59.5 mm |
| Inside diameter of flange (d2) | 13 mm | Flange width (b) | 26 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001051 | ETIM 9.0 | EC001051 |
| ETIM 10.0 | EC001051 | ECLASS 14.0 | 27-40-02-05 |
| ECLASS 15.0 | 27-40-02-05 | | |

KRN-M12/-185 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

