

KRN-M6/-4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end,4 mm ² ,4 mm ² - 4 mm ²
Order No.	1495150000
Type	KRN-M6/-4
GTIN (EAN)	4050118305067
Qty.	100 items

KRN-M6/-4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	2.56 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	Euro series, standard
---------	-----------------------

Connectors

Conductor cross-section, max.	4 mm ²	Conductor cross-section, min.	4 mm ²
Conductor cross-section	4 mm ²	Insulation	not available
Hole	M 6	Identification colour	None
Inside diameter of shaft (d1)	3 mm	Outside diameter of shaft (d3)	5 mm
Shaft length (a)	8 mm	Connection length (l)	20 mm
Inside diameter of flange (d2)	6.4 mm	Flange width (b)	11 mm

Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

KRN-M6/-4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

