

**KWN-M16/-150 45****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end, 150 mm <sup>2</sup> , 150 mm <sup>2</sup> - 150 mm <sup>2</sup>
Order No.	<a href="#">1496470000</a>
Type	KWN-M16/-150 45
GTIN (EAN)	4050118306132
Qty.	25 items

## KWN-M16/-150 45

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	98.92 g
------------	---------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Version	Euro series, 45°
---------	------------------

### Connectors

Conductor cross-section, max.	150 mm <sup>2</sup>	Conductor cross-section, min.	150 mm <sup>2</sup>
Conductor cross-section	150 mm <sup>2</sup>	Insulation	not available
Hole	M 16	Identification colour	None
Inside diameter of shaft (d1)	16.8 mm	Outside diameter of shaft (d3)	21.3 mm
Shaft length (a)	28 mm	Inside diameter of flange (d2)	17 mm
Flange width (b)	31 mm		

### Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

**KWN-M16/-150 45**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

