

**KP-M10/-120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end, 120 mm <sup>2</sup>
Order No.	<a href="#">1498240000</a>
Type	KP-M10/-120
GTIN (EAN)	4050118307368
Qty.	50 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	115.24 g
------------	----------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Version	DIN series 46235, standard
---------	-------------------------------

### Connectors

Conductor cross-section	120 mm <sup>2</sup>	Insulation	not available
Hole	M10	Inside diameter of shaft (d1)	15.5 mm
Outside diameter of shaft (d3)	21 mm	Shaft length (a)	35 mm
Connection length (l)	70 mm	Inside diameter of flange (d2)	10.5 mm
Flange width (b)	31 mm	Identification number Cu	20 K

### Classifications

ETIM 8.0	EC001050	ETIM 9.0	EC001050
ETIM 10.0	EC001050	ECLASS 14.0	27-40-02-03
ECLASS 15.0	27-40-02-03		

Drawings

