

VPN/-240**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|-----------------|--|
| Version | cable lug, terminal end,240 mm ² ,240 mm ² ,None |
| Order No. | 1498730000 |
| Type | VPN/-240 |
| GTIN (EAN) | 4050118308044 |
| Qty. | 15 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2026-03-31T00:00:00+02:00 |

VPN/-240

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|-------|
| Net weight | 232 g |
|------------|-------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Connectors

| | | | |
|-------------------------------|---------------------|--------------------------------|---------------------|
| Conductor cross-section, max. | 240 mm ² | Conductor cross-section | 240 mm ² |
| Insulation | not available | Inside diameter of shaft (d1) | 21.5 mm |
| Length 2 (l2) | 7 mm | Outside diameter of shaft (d3) | 29 mm |
| Connection length (l) | 90 mm | Identification number Cu | 28 K |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001059 | ETIM 9.0 | EC001059 |
| ETIM 10.0 | EC001059 | ECLASS 14.0 | 27-40-02-12 |
| ECLASS 15.0 | 27-40-02-12 | | |

Drawings



VPN/-240

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

... for tubular cable lugs (acc. to EN 13600)



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

| | | | |
|------------|----------------------------|-------------------------------|--|
| Type | ES APG 80 WM 240 | Version | |
| Order No. | 1502580000 | 240mm ² , WM crimp | |
| GTIN (EAN) | 4050118310689 | | |
| Qty. | 1 ST | | |

... for compression cable lugs (acc. to DIN 46235)



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

| | | | |
|------------|----------------------------|--------------------------------------|--|
| Type | ES APG 80 HEX 240 | Version | |
| Order No. | 1502740000 | 240mm ² , Hexagonal crimp | |
| GTIN (EAN) | 4050118310481 | | |
| Qty. | 1 ST | | |