


**CC-M 27/70 2X3 ST****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 27 x 70 mm, silver
Order No.	<a href="#">1500190000</a>
Type	CC-M 27/70 2X3 ST
GTIN (EAN)	4050118309003
Qty.	80 items

**CC-M 27/70 2X3 ST**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	27 mm	Height (inches)	1.063 inch
Width	70 mm	Width (inches)	2.7559 inch
Net weight	6.18 g		

**Temperatures**

Operating temperature range -55...130 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Version	pluggable, with 3.5 mm mounting hole		
Width	70 mm		
Operating temperature range, max.	130 °C		
Operating temperature range, min.	-55 °C		
Colour	silver		
Basic material	Stainless steel 1.4301		
Printed characters	without		
Number of markers per packaging unit	Form of supply	MetalliCard	
Size of labelling field	68.3 x 25.3 mm		
Recommended industries	Energy, Process		
compatible printer			
Number of markers per combination	1 MetalliCard = Device markers		
Operating temperature range	-55...130 °C		

**Device markers**

Drill-hole diameter 3.00 mm

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**CC-M 27/70 2X3 ST**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Example of use**



## CC-M 27/70 2X3 ST

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Complementary products



### General ordering data

Type	INLAY CC-M 27/70	Version	
Order No.	<a href="#">1500290000</a>		
GTIN (EAN)	4050118309034		
Qty.	1 ST		
Type	PRIMER CC-M	Version	
Order No.	<a href="#">2068020000</a>		
GTIN (EAN)	4050118416534		
Qty.	100 ST		