

INLAY SFX-M 12/40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties. A special punching in the SFX-M allows the use of steel cable ties. For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Order No.	1500320000
Type	INLAY SFX-M 12/40
GTIN (EAN)	4050118308945
Qty.	1 items

INLAY SFX-M 12/40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	120 mm	Depth (inches)	4.7244 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	75 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	Holder for 5 signs	Width	76 mm
---------	--------------------	-------	-------

Classifications

ETIM 8.0	EC001675	ETIM 9.0	EC001675
ETIM 10.0	EC001675	ECLASS 14.0	19-14-90-90
ECLASS 15.0	19-14-90-90		