

PZ RK 10/120**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for tubular and compression cable lugs with swivel crimping star.

- Integrated crimping star for different cross-sections
- Hexagon crimping tools for compression cable lugs
- WM-From crimping tools for tubular cable lugs
- wide processing range up to 70 or 120 mm²

General ordering data

Version	10mm ² , 120mm ² , Hexagonal crimp
Order No.	1500450000
Type	PZ RK 10/120
GTIN (EAN)	4050118309065
Qty.	1 items

Technical data

Dimensions and weights

Depth	660 mm	Depth (inches)	25.9842 inch
Net weight	3760 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Crimp inserts

Crimping width	5 mm
----------------	------

Description of contact

Crimping range, max.	120 mm ²	Crimping range, min.	10 mm ²
----------------------	---------------------	----------------------	--------------------

tool data crimping

Wire end ferrules cross-section, max.	120 mm ²	Wire end ferrules cross-section, min.	10 mm ²
Crimping type/profile	Hexagonal crimp		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		