

ES EPG 45 WM 95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	95mm ² , WM crimp
Order No.	1500890000
Type	ES EPG 45 WM 95
GTIN (EAN)	4050118309218
Qty.	1 items

ES EPG 45 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12 mm	Depth (inches)	0.4724 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	136 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	5 mm	Crimp cross-section copper	95
Crimping width in mm	5		

Description of contact

Conductor cross-section, max. AWG	3/0	Conductor cross-section, min. AWG	3/0
Crimping range, max.	95 mm ²		

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 95 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG 45 WM 95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools




Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 45	Version
Order No.	1500830000	Pressing tool, 6mm ² , 150mm ² , Hexagonal crimp, WM crimp, Indent
GTIN (EAN)	4050118309317	crimp, Trapezoidal crimp, Oval crimping
Qty.	1 ST	

95 mm²95 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-95 S	Version
Order No.	1494430000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118303957	
Qty.	25 ST	
Type	KRN-M8/-95 S	Version
Order No.	1494890000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304121	
Qty.	25 ST	
Type	KRN-M10/-95 S	Version
Order No.	1494900000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304398	
Qty.	25 ST	
Type	KRN-M12/-95 S	Version
Order No.	1494910000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304510	
Qty.	25 ST	

ES EPG 45 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M8/-95 90	Version
Order No.	1496080000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305685	
Qty.	25 ST	
Type	KWN-M10/-95 90	Version
Order No.	1496090000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305692	
Qty.	25 ST	
Type	KWN-M12/-95 90	Version
Order No.	1496100000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305487	
Qty.	25 ST	
Type	KWN-M14/-95 90	Version
Order No.	1494670000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304411	
Qty.	25 ST	
Type	KWN-M16/-95 90	Version
Order No.	1496110000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305678	
Qty.	25 ST	
Type	KWN-M8/-95 45	Version
Order No.	1496340000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305821	
Qty.	25 ST	
Type	KWN-M10/-95 45	Version
Order No.	1496350000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118306125	
Qty.	25 ST	
Type	KWN-M12/-95 45	Version
Order No.	1496370000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305890	
Qty.	25 ST	
Type	KWN-M16/-95 45	Version
Order No.	1496380000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305838	
Qty.	25 ST	
Type	KP-M8/-95	Version
Order No.	1498180000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307498	
Qty.	50 ST	
Type	KP-M10/-95	Version
Order No.	1498190000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307603	
Qty.	50 ST	
Type	KP-M12/-95	Version
Order No.	1498210000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307610	
Qty.	50 ST	
Type	KP-M14/-95	Version
Order No.	1498520000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307863	
Qty.	50 ST	

ES EPG 45 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KP-M16/-95	Version
Order No.	1498220000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307719	
Qty.	50 ST	
Type	KP-M20/-95	Version
Order No.	1498230000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307634	
Qty.	50 ST	
Type	KWPN-M8/-95 90	Version
Order No.	1497690000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307207	
Qty.	25 ST	
Type	KWPN-M10/-95 90	Version
Order No.	1497710000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307139	
Qty.	25 ST	
Type	KWPN-M12/-95 90	Version
Order No.	1497720000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307214	
Qty.	25 ST	
Type	KWPN-M16/-95 90	Version
Order No.	1497730000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307054	
Qty.	25 ST	
Type	VPN/-95	Version
Order No.	1498680000	cable lug, terminal end,95 mm ² ,95 mm ² ,None
GTIN (EAN)	4050118307917	
Qty.	50 ST	
Type	VPLN/-95	Version
Order No.	1492950000	cable lug, terminal end,95 mm ² ,95 mm ² ,None
GTIN (EAN)	4050118302622	
Qty.	50 ST	
Type	KRN-M6/-95	Version
Order No.	1495820000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305531	
Qty.	25 ST	
Type	KRN-M8/-95	Version
Order No.	1495600000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305241	
Qty.	25 ST	
Type	KRN-M10/-95	Version
Order No.	1495610000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305371	
Qty.	25 ST	
Type	KRN-M12/-95	Version
Order No.	1495620000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305265	
Qty.	25 ST	
Type	KRN-M14/-95	Version
Order No.	1495780000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305555	
Qty.	25 ST	

ES EPG 45 WM 95

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	KRN-M16/-95	Version	
Order No.	1495630000		cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305326		
Qty.	25 ST		
Type	KRN-M20/-95	Version	
Order No.	1495640000		cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305319		
Qty.	25 ST		