


**ES EPG 45 AEH 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Version	25mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">1501070000</a>
Type	ES EPG 45 AEH 25
GTIN (EAN)	4050118309164
Qty.	1 items

**ES EPG 45 AEH 25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 160.16 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Crimp inserts**

Crimping width 19 mm Crimp cross-section copper 25

**Description of contact**

Conductor cross-section, max. AWG 4 Conductor cross-section, min. AWG 4  
 Crimping range, max. 25 mm<sup>2</sup>

**tool data crimping**

Crimping type/profile Trapezoidal crimp  
 Cable lug cross section nominal 25 mm<sup>2</sup>

**Classifications**

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		