


ES EPG 45 AEH 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	35mm ² , Trapezoidal crimp
Order No.	1501170000
Type	ES EPG 45 AEH 35
GTIN (EAN)	4050118309386
Qty.	1 items

ES EPG 45 AEH 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	180 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	19 mm	Crimp cross-section copper	35
----------------	-------	----------------------------	----

Description of contact

Conductor cross-section, max. AWG	2	Conductor cross-section, min. AWG	2
Crimping range, max.	35 mm ²		

tool data crimping

Crimping type/profile	Trapezoidal crimp		
Cable lug cross section	nominal		35 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		