

**ES APG 80 WM 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
  - electronic control and monitoring of the crimping process
  - Saving of all crimping cycles and error messages to internal memory
  - Reading of all cycles and error messages via USB

**General ordering data**

|            |                              |
|------------|------------------------------|
| Version    | 25mm <sup>2</sup> , WM crimp |
| Order No.  | <a href="#">1502480000</a>   |
| Type       | ES APG 80 WM 25              |
| GTIN (EAN) | 4050118310634                |
| Qty.       | 1 items                      |

**ES APG 80 WM 25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 351.9 g |
|------------|---------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Crimp inserts**

|                      |       |                            |    |
|----------------------|-------|----------------------------|----|
| Crimping width       | 12 mm | Crimp cross-section copper | 25 |
| Crimping width in mm | 12    |                            |    |

**Description of contact**

|                                   |                    |                                   |   |
|-----------------------------------|--------------------|-----------------------------------|---|
| Conductor cross-section, max. AWG | 4                  | Conductor cross-section, min. AWG | 4 |
| Crimping range, max.              | 25 mm <sup>2</sup> |                                   |   |

**tool data crimping**

|                         |                            |
|-------------------------|----------------------------|
| Crimping type/profile   | WM crimp                   |
| Cable lug cross section | nominal 25 mm <sup>2</sup> |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001282    | ETIM 9.0    | EC001282    |
| ETIM 10.0   | EC001282    | ECLASS 14.0 | 21-04-90-90 |
| ECLASS 15.0 | 21-04-90-90 |             |             |