


ES APG 80 WM 70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
 - electronic control and monitoring of the crimping process
 - Saving of all crimping cycles and error messages to internal memory
 - Reading of all cycles and error messages via USB

General ordering data

Version	70mm ² , WM crimp
Order No.	1502520000
Type	ES APG 80 WM 70
GTIN (EAN)	4050118310580
Qty.	1 items

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 342.3 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Crimp inserts

Crimping width 12 mm Crimp cross-section copper 70
 Crimping width in mm 12

Description of contact

Conductor cross-section, max. AWG 2/0 Conductor cross-section, min. AWG 2/0
 Crimping range, max. 70 mm²

tool data crimping

Crimping type/profile WM crimp
 Cable lug cross section nominal 70 mm²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		