

**ES APG 80 HEX 185****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
  - electronic control and monitoring of the crimping process
  - Saving of all crimping cycles and error messages to internal memory
  - Reading of all cycles and error messages via USB

**General ordering data**

Version	185mm <sup>2</sup> , Hexagonal crimp
Order No.	<a href="#">1502730000</a>
Type	ES APG 80 HEX 185
GTIN (EAN)	4050118310726
Qty.	1 items

**ES APG 80 HEX 185**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight	298.2 g
------------	---------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Crimp inserts**

Identification number	25	Crimping width	5 mm
Crimp cross-section aluminium	150	Crimp cross-section copper	185
Crimping width in mm	5		

**Description of contact**

Conductor cross-section, max. AWG	6/0	Conductor cross-section, min. AWG	6/0
Crimping range, max.	185 mm <sup>2</sup>		

**tool data crimping**

Crimping type/profile	Hexagonal crimp		
Cable lug cross section	nominal	185 mm <sup>2</sup>	

**Classifications**

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		