

ES APG 80 DIN 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
 - electronic control and monitoring of the crimping process
 - Saving of all crimping cycles and error messages to internal memory
 - Reading of all cycles and error messages via USB

General ordering data

| | |
|------------|----------------------------------|
| Version | 35mm ² , Indent crimp |
| Order No. | 1502870000 |
| Type | ES APG 80 DIN 35 |
| GTIN (EAN) | 4050118310474 |
| Qty. | 1 items |

ES APG 80 DIN 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 351.7 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Crimp inserts

Crimping width 11 mm Crimp cross-section copper 35
 Crimping width in mm 11

Description of contact

Conductor cross-section, max. AWG 2 Conductor cross-section, min. AWG 2
 Crimping range, max. 35 mm²

tool data crimping

Crimping type/profile Indent crimp
 Cable lug cross section nominal 35 mm²

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001282 | ETIM 9.0 | EC001282 |
| ETIM 10.0 | EC001282 | ECLASS 14.0 | 21-04-90-90 |
| ECLASS 15.0 | 21-04-90-90 | | |