

**ES APG 80 DIN 95****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
  - electronic control and monitoring of the crimping process
  - Saving of all crimping cycles and error messages to internal memory
  - Reading of all cycles and error messages via USB

**General ordering data**

Version	95mm <sup>2</sup> , Indent crimp
Order No.	<a href="#">1502900000</a>
Type	ES APG 80 DIN 95
GTIN (EAN)	4050118310917
Qty.	1 items

**ES APG 80 DIN 95**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 340.3 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Crimp inserts**

Crimping width 16 mm Crimp cross-section copper 95  
 Crimping width in mm 16

**Description of contact**

Conductor cross-section, max. AWG 3/0 Conductor cross-section, min. AWG 3/0  
 Crimping range, max. 95 mm<sup>2</sup>

**tool data crimping**

Crimping type/profile Indent crimp  
 Cable lug cross section nominal 95 mm<sup>2</sup>

**Classifications**

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		