

**HSS-HF 6.4-12.7 EL Y30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 6.4 - 12.7 mm, yellow
Order No.	<a href="#">1513200000</a>
Type	HSS-HF 6.4-12.7 EL Y30M
GTIN (EAN)	4050118320923
Qty.	1 items

## HSS-HF 6.4-12.7 EL Y30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Width	20.9 mm	Width (inches)	0.8228 inch
Length	30000 mm	Length (inches)	1181.1 inch
Net weight	722 g		

### Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	Width	20.9 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	No
Length	30000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>
Operating temperature range	-55...105 °C	Number per roll	1

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	35 mm <sup>2</sup>
Conductor cross-section, min.	6 mm <sup>2</sup>	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	6.4 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	6.4 - 12.7 mm
Cross-section for connected wire	6 - 35 mm <sup>2</sup>		

### Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



## HSS-HF 6.4-12.7 EL Y30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

Type	RIBBON HSS HF EL 40/300...	Version	
Order No.	<a href="#">1426210000</a>	Ink ribbon	
GTIN (EAN)	4050118228823		
Qty.	1 ST		

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

Type	THM MMP EXT.RH	Version	
Order No.	<a href="#">1302920000</a>		
GTIN (EAN)	4050118102307		
Qty.	1 ST		
Type	MULTIMARK ROLLER 115	Version	
Order No.	<a href="#">1357420000</a>		
GTIN (EAN)	4050118160314		
Qty.	1 ST		
Type	MULTIMARK ROLLER 30	Version	
Order No.	<a href="#">1357430000</a>		
GTIN (EAN)	4050118160253		
Qty.	1 ST		

## HSS-HF 6.4-12.7 EL Y30M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	<a href="#">2672590000</a>		
GTIN (EAN)	4050118708097		
Qty.	1 ST		