

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 4.8 - 9.5 mm, white
Order No.	1513290000
Type	HSS-HF 4.8-9.5 EL W30M
GTIN (EAN)	4050118320848
Qty.	1 items

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Width	15.1 mm	Width (inches)	0.5945 inch
Length	30000 mm	Length (inches)	1181.1 inch
Net weight	494.56 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	15.1 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	white	Halogen	No
Length	30000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...105 °C	Number per roll	1

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	4 mm ²	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	4.8 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	4.8 - 9.5 mm
Cross-section for connected wire	4 - 16 mm ²		

Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON HSS HF EL 40/300...	Version
Order No.	1426210000	Ink ribbon
GTIN (EAN)	4050118228823	
Qty.	1 ST	

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP EXT.RH	Version
Order No.	1302920000	
GTIN (EAN)	4050118102307	
Qty.	1 ST	
Type	MULTIMARK ROLLER 115	Version
Order No.	1357420000	
GTIN (EAN)	4050118160314	
Qty.	1 ST	
Type	MULTIMARK ROLLER 30	Version
Order No.	1357430000	
GTIN (EAN)	4050118160253	
Qty.	1 ST	

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		