

**SAI-10L-VPFC-4A-M08L-PNP-05U06**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

The new slim M8 line from Weidmüller. This range of products is characterised by the marking options at all connection positions. Even the 4-way distributor with 8-pole M12 has adequately large markers at all M8 connection positions. Furthermore, this distributor is shorter than many conventional M8 designs.

- Very narrow, short and flat M8 distributor.
- The range is supplied with 4 to 12 M8 connection positions, 3 or 4 poles.
- Hybrid variants of the M8 are also possible on request.
- The M8 line is equipped with transverse holes.

**General ordering data**

Version	Fixed cable version, M8, 30 V, , LED: Yes, LED initiator: Yes, Wiring type: , 5 m
Order No.	<a href="#">1529470000</a>
Type	SAI-10L-VPFC-4A-M08L-PNP-05U06
GTIN (EAN)	4050118334258
Qty.	1 items

## SAI-10L-VPFC-4A-M08L-PNP-05U06

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

### Dimensions and weights

Depth	19.2 mm	Depth (inches)	0.7559 inch
Height	170 mm	Height (inches)	6.6929 inch
Width	24 mm	Width (inches)	0.9449 inch
Net weight	300 g		

### Temperatures

Operating temperature -25 - 80°C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### Connection data

Sheathing stripping length 100 mm Distributor outlet Fixed cable version

### Electrical data

Rated voltage, min.	15 V	Rated voltage, max.	30 V
Test voltage	1 kV	Max. current-carrying capacity per slot	2 A
Total current	6 A	Current per signal	1 A
Electrical isolation available	No		

### General technical data

Protection degree	IP68	Number of poles	4
Number of contact sockets	10	Connection thread	M8
Pollution severity	3	Fire behaviour	V-0
LED	Yes	LED initiator	Yes
LED colour for indicating operation	green	LED colour for I/O function	yellow

### Material data

Material O-Ring	FKM	Housing main material	PBT
Material of distributor	Plastic	Housing colour	black (similar to RAL 9005)
Screw socket	Nickel-plated CuZn	Contact material	CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 V0)

### Technical data cable

Number of poles	4	Sheathing colour	black
O.D.	7.7 mm	Shielded	No

Creation date 24.02.2026 02:34:30 MEZ

Catalogue status / Drawings

**SAI-10L-VPFC-4A-M08L-PNP-05U06**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Halogen	No	Bending radius, min., moving	10 x cable diameter
Bending cycles	2 Mio	Wire cross section (Print/Online)	12 x 0.34 mm <sup>2</sup> + 2 x 0.75 mm <sup>2</sup>
Sheath material	PUR	Cable length	5 m
Suitable for cable carriers	Yes		

**Classifications**

ETIM 8.0	EC002585	ETIM 9.0	EC002585
ETIM 10.0	EC002585	ECLASS 14.0	27-44-01-08
ECLASS 15.0	27-44-01-08		


SAI-10L-VPFC-4A-M08L-PNP-05U06

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


Drawings

www.weidmueller.com

Dimensioned drawing



Wiring diagram



Pole scheme

