

IE-FC-SET-SPDED001-KN-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

| | |
|------------|----------------------------|
| Version | FrontCom, Set |
| Order No. | 1529580000 |
| Type | IE-FC-SET-SPDED001-KN-P |
| GTIN (EAN) | 4050118334432 |
| Qty. | 1 items |

IE-FC-SET-SPDED001-KN-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 134 mm | Depth (inches) | 5.2756 inch |
| Height | 40 mm | Height (inches) | 1.5748 inch |
| Width | 67 mm | Width (inches) | 2.6378 inch |
| Net weight | 451 g | | |

Temperatures

Storage temperature _____ Operating temperature _____
 Installation temperature _____

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3
 SCIP 8a473a8a-33d4-4318-8088-c28f019e7f77

General data

| | | | |
|-------------------|---|----------------------------------|--|
| Product type | Set | | |
| Protection degree | IP65, in closed state | | |
| Material frame | Zinc diecast | | |
| Material cover | Polycarbonate PC | | |
| Reference product | IE-FC-SFP-KNOB , IE-FC-SP-PWB/2ST , IE-FC-I-PWB-DE , IE-BI-USB-A , IE-BI-RJ45-C | | |
| Reference product | Cardinality | 1 | |
| | Reference | IE-FC-SFP-KNOB | |
| | Cardinality | 1 | |
| | Reference | IE-FC-SP-PWB/2ST | |
| | Cardinality | 1 | |
| | Reference | IE-FC-I-PWB-DE | |
| | Cardinality | 1 | |
| | Reference | IE-BI-USB-A | |
| Cardinality | 1 | | |
| Reference | IE-BI-RJ45-C | | |

Technical data

| | | | |
|--------------------------|-----------------------------------|--------------------------|---------------|
| Insert plate | 2x data, 1x power, Shielded | Frame | Plastic cover |
| Rated voltage for socket | 250 V | Power inserts | Socket DE |
| Data inserts | USB 2.0 A/A, RJ45 coupling Cat.6A | Rated current for socket | 16 A |

General standards

Certificate No. (DNV) TAA000022B

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001031 | ETIM 9.0 | EC001031 |
| ETIM 10.0 | EC001031 | ECLASS 14.0 | 27-18-28-92 |
| ECLASS 15.0 | 27-18-28-92 | | |

IE-FC-SET-SPDED001-KN-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

