

BUGH BOX WM4 C BT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



WM4 C photovoltaic connectors

- one crimp contact for 4 mm² and 6 mm² cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

General ordering data

Version	Photovoltaics, Plug-in connector, female
Order No.	1530630000
Type	BUGH BOX WM4 C BT
GTIN (EAN)	4050118335453
Qty.	100 items

BUGH BOX WM4 C BT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 5.5 g

Temperatures

Continuous operating temp., min. -40 °C Continuous operating temp., max. 85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical data

Outer cable diameter, max.	7 mm	Outer cable diameter, min.	5.5 mm
Cable type	2 Pfg 1169/08.07, EN 50618:2014	Approvals	TÜV Rheinland (IEC 62852)
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Protection degree	IP65, IP67, IP2x open	Pollution severity	2
Rated voltage	1500 V DC (IEC)	External thread	M 12
Rated current	35 A		

Guarantee

Time interval 2 years

Important note

Product information Please order contacts separately

Classifications

ETIM 8.0	EC002928	ETIM 9.0	EC002928
ETIM 10.0	EC002928	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		