

## SFGH WM4 C BT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### WM4 C photovoltaic connectors

- one crimp contact for 4 mm<sup>2</sup> and 6 mm<sup>2</sup> cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

### General ordering data

Version	Photovoltaics, Plug-in connector, male
Order No.	<a href="#">1530700000</a>
Type	SFGH WM4 C BT
GTIN (EAN)	4050118335330
Qty.	100 items

**SFGH WM4 C BT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 13.8 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

**Technical data**

Outer cable diameter, max.	7 mm	Outer cable diameter, min.	5.5 mm
Cable type	2 Pfg1 169/08.07, EN 50618:2014	Approvals	TÜV Rheinland (IEC 62852)
Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
Protection degree	IP65, IP67, IP2x open	Pollution severity	2
Rated voltage	1500 V DC (IEC)	External thread	M 16
Rated current	35 A		

**Guarantee**

Time interval 2 years

**Important note**

Product information Please order contacts separately

**Classifications**

ETIM 8.0	EC002928	ETIM 9.0	EC002928
ETIM 10.0	EC002928	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		