

POWERSTRIPPER AM 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Electric drive

General ordering data

Version	Tools, Automatic stripper
Order No.	1534740000
Type	POWERSTRIPPER AM 12
GTIN (EAN)	4050118338409
Qty.	1 items

POWERSTRIPPER AM 12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	230 mm	Depth (inches)	9.0551 inch
Height	520 mm	Height (inches)	20.4724 inch
Width	254 mm	Width (inches)	10 inch
Net weight	17000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Automatic stripping

Drive	Electropneumatic	Pulse time	approx. 3 s
Pull-off length	20 - 120 mm	Compressed-air connection	5 - 5.5 bar
Electrical connection	100 - 240 V / 50/60 Hz / 16 VA	Max. dismantling length	120 mm
Max. dismantling area	11.90	Insertion length	80 mm
Min. dismantling length	25 mm	Min. dismantling area	3.5 mm

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

POWERSTRIPPER AM 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

