


## CRIMPSET PZ 10 SQR D

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Crimp sets

#### General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 10 SQR, Stripping tool: STRIPAX, Crimping range, min.: 0.14, Colour code: DIN
Order No.	<a href="#">1542290000</a>
Type	CRIMPSET PZ 10 SQR D
GTIN (EAN)	4050118347128
Qty.	1 items
Packaging	Plastic box

## CRIMPSET PZ 10 SQR D

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1591.04 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

### Technical data

Description of article	Set includes crimping tool up to 10 mm <sup>2</sup> square, stripping tool and wire-end ferrules in DIN colour code
------------------------	---

### Assortments

Crimping range, max.	10 mm <sup>2</sup>	Crimping range, min.	0.14 mm <sup>2</sup>
Packaging	Plastic box	Stripping tool	STRIPAX
Crimping tool	PZ 10 SQR	Colour code	DIN
Number of AEH	2900 pcs.		

### Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

## CRIMPSET PZ 10 SQR D

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

### General ordering data

Type	STRIPAX	Version	
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

### Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Type	PZ 10 SQR	Version	
Order No.	<a href="#">1445080000</a>	Crimping tool for wire-end ferrules, 0.14mm <sup>2</sup> , 10mm <sup>2</sup> , Square crimp	
GTIN (EAN)	4050118250152		
Qty.	1 ST		

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

## CRIMPSET PZ 10 SQR D

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H0,5/14D W	Version
Order No.	<a href="#">9019010000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190120931	
Qty.	500 ST	
Type	H0,75/14D GR	Version
Order No.	<a href="#">9019040000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190099077	
Qty.	500 ST	
Type	H1,0/14D R	Version
Order No.	<a href="#">9019080000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190090623	
Qty.	500 ST	
Type	H1,5/14D SW	Version
Order No.	<a href="#">9019120000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190153793	
Qty.	500 ST	
Type	H2,5/15D BL	Version
Order No.	<a href="#">9019160000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190028732	
Qty.	500 ST	
Type	H4,0/20D GR	Version
Order No.	<a href="#">9019200000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190126575	
Qty.	500 ST	

### Conductor nom. cross-section 6.0mm<sup>2</sup>



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H6,0/20D GE	Version
Order No.	<a href="#">9019220000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow
GTIN (EAN)	4008190151607	
Qty.	100 ST	

## CRIMPSET PZ 10 SQR D

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Conductor nom. cross-section 10mm<sup>2</sup>



10 mm<sup>2</sup>

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H10,0/22D R	Version	
Order No.	<a href="#">9019240000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, red	
GTIN (EAN)	4008190075385		
Qty.	100 ST		

### Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

### General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	<a href="#">9028860000</a>	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		