

IE-FCI-PWCB-3A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, Front-Com® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the Front-Com® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

| | |
|------------|-----------------------------|
| Version | FrontCom, Fuse, Fuse insert |
| Order No. | 1543690000 |
| Type | IE-FCI-PWCB-3A |
| GTIN (EAN) | 4050118348859 |
| Qty. | 1 items |

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E479289 |

Dimensions and weights

| | |
|------------|------|
| Net weight | 37 g |
|------------|------|

Temperatures

| | |
|--------------------------|-----------------------|
| Storage temperature | Operating temperature |
| Installation temperature | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 8bl |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--------------|------|-------------|-------------|
| Product type | Fuse | Insert type | Fuse insert |
|--------------|------|-------------|-------------|

General standards

| | | | |
|-----------------------|------------|----------------------|---------|
| Certificate No. (DNV) | TAA000022B | Certificate No. (UR) | E479289 |
|-----------------------|------------|----------------------|---------|

Technical data

| | | | |
|---------------------------|-------------------------------|-------------------|-------------------|
| Type of connection | Flat-blade receptacles 6.5 mm | Nominal current | 3 A |
| Resistance | 0,069 Ω typ. | Operating voltage | 32 V DC, 250 V AC |
| Current-carrying capacity | 1.5 kVeff | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001121 | ETIM 9.0 | EC001121 |
| ETIM 10.0 | EC001121 | ECLASS 14.0 | 27-44-03-90 |
| ECLASS 15.0 | 27-44-03-90 | | |