

**SAI-SUB-D 9 SK35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

Version	SUB-D
Order No.	<a href="#">1551080000</a>
Type	SAI-SUB-D 9 SK35
GTIN (EAN)	4050118357707
Qty.	1 items

## SAI-SUB-D 9 SK35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	16.8 mm	Depth (inches)	0.6614 inch
Height	64.5 mm	Height (inches)	2.5394 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	20 g		

## Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6al
REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

## Technical specifications for sub-D connector

Tightening torque	0.3 Nm	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Protection degree	IP30
Plugging cycles	≥ 200	Outgoing elbow	35°
Terminating resistor available	No	BUS interface	D-Sub 9-pole, Pin
Interlock	UNC4-40	Temperature range of housing	-20...+70 ° C
BUS, cable interface	Screw connection	Programming interface	No

## Classifications

ETIM 8.0	EC001132	ETIM 9.0	EC001132
ETIM 10.0	EC001132	ECLASS 14.0	27-44-03-02
ECLASS 15.0	27-44-03-22		