
Data sheet

SAI-SUB-D 9 SK35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Version	SUB-D
Order No.	1551080000
Type	SAI-SUB-D 9 SK35
GTIN (EAN)	4050118357707
Qty.	1 items

SAI-SUB-D 9 SK35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	16.8 mm	Depth (inches)	0.6614 inch
Height	64.5 mm	Height (inches)	2.5394 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	20 g		

Temperatures

Humidity	Max. 75% at +25°C, non-condensing

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6aI
REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

Technical specifications for sub-D connector

Tightening torque	0.3 Nm	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Protection degree	IP30
Plugging cycles	≥ 200	Outgoing elbow	35°
Terminating resistor available	No	BUS interface	D-Sub 9-pole, Pin
Interlock	UNC4-40	Temperature range of housing	-20...+70 ° C
BUS, cable interface	Screw connection	Programming interface	No

Classifications

ETIM 8.0	EC001132	ETIM 9.0	EC001132
ETIM 10.0	EC001132	ECLASS 14.0	27-44-03-02
ECLASS 15.0	27-44-03-22		